

# DSP1\*

## DIRECTIONAL VALVES, PILOT OPERATED, SOLENOID OR HYDRAULIC (DSC1\*) ACTUATED

### SUBPLATE MOUNTING


**DS\*10 ISO 4401-10**

**DS\*11 ISO 4401-10** oversize ports

**p max 350 bar**

**Q max 1600 l/min**

### OPERATING PRINCIPLE



- The DSP10 and DSP11 are 4-ports directional valves, pilot operated, solenoid actuated, with mounting surface according to ISO 4401-10 standards. The DS\*11 valves have ports Ø48.
- The directional valves DSC10 and DSC11 are the versions with hydraulic actuation.
- They are available with different spool types (see point 2) and with some options for the opening control.
- The DSP\* valves are available with internal or external pilot supply and internal or external drain. A version with internal pilot supply with fixed pressure reducing valve is also available.

### PERFORMANCES

(obtained with mineral oil of viscosity of 36 cSt at 50°C)

		<b>DS*10</b>	<b>DS*11</b>
Maximum operating pressure	bar	350 300 210 (DC) / 160 (AC)	350 300 210 (DC) / 160 (AC)
- ports P - A - B (standard version)			
- port T (external drainage)			
- port T (internal drainage)			
Maximum flow rate from port P to A - B - T	l/min	1100	1600
Ambient temperature range	°C	-20 / +50	
Fluid temperature range	°C	-20 / +80	
Fluid viscosity range	cSt	10 ÷ 400	
Fluid contamination degree	according to ISO 4406:1999 class 20/18/15		
Recommended viscosity	cSt	25	
Mass: DSP	kg	40.8	38
DSC		39.5	36.7

## 1 - IDENTIFICATION CODE FOR SOLENOID ACTUATED DIRECTIONAL VALVES

<b>D</b>	<b>S</b>	<b>P</b>	-	/	-	/	/	<b>K1</b>	/	
----------	----------	----------	---	---	---	---	---	-----------	---	--

Pilot operated directional valve, solenoid actuated

**10** = ISO 4401-10 size  
**11** = ISO 4401-10 with oversize ports

Spool type (see point 2)

**S\*** TA  
**SA\*** TB  
**SB\*** RK\*

Series:

**21** = for DSP10  
**12** = for DSP11  
 (the overall dimensions do not change within the same ten)

Seals:

**N** = NBR seals for mineral oil (**standard**)  
**V** = FPM seals for special fluids

Pilot supply (see points 10 and 11):

**I** = Internal (not available for spools S2 - S4 - TA02 - TB02 - RK02 - S\*2 - S\*4)  
**E** = External  
**Z** = Internal pilot supply with 30 bar pressure reducing valve, fixed adjustment.

Drainage (see points 10 and 11):

**I** = Internal  
**E** = External

Controls (see point 16):

Omit if not required.

**C** = Main spool stroke control  
**D** = Main spool switching speed control  
**P15** = Subplate placed under the pilot stage with restrictor of Ø1.5 in P port

**NOTE:** The locking rings of the coils and the relevant O-rings are supplied.

Manual override:  
 Omit for override integrated in the tube (**standard**)  
**CM** = Manual override, boot protected (see point 17)

Coil electrical connection:  
 plug for connector type EN 175301-803 (ex DIN 43650)

Power supply (see point 8)

Direct current





**D12** = 12 V  
**D24** = 24 V  
**D48** = 48 V  
**D110** = 110 V  
**D220** = 220 V  
**D00** = Valve without coils (see **NOTE**)

Alternate current



**A24** = 24 V - 50 Hz  
**A48** = 48 V - 50 Hz  
**A110** = 110 V - 50 Hz / 120 V - 60 Hz  
**A230** = 230 V - 50 Hz / 240 V - 60 Hz  
**A00** = Valve without coils (see **NOTE**)  
**F110** = 110 V - 60 Hz  
**F220** = 220 V - 60 Hz

## 2 - DSP10 AND DSP11 SPOOLS TYPES






**Type S\*:**  
2 solenoids - 3 positions  
with spring centering





**Type SA\*:**  
1 solenoid side A  
2 positions (central + external)  
with spring centering






**Type SB\*:**  
1 solenoid side B  
2 positions (central + external)  
with spring centering





**Type RK:**  
2 solenoids - 2 positions  
with mechanical retention



**Type TA:**  
1 solenoid side A  
2 external positions  
with return spring




**Type TB:**  
1 solenoid side B  
2 external positions  
with return spring



Please consult our Technical Department for other types of spools.

### 3 - IDENTIFICATION CODE FOR HYDRAULIC ACTUATED DIRECTIONAL VALVES



### 4 - HYDRAULIC FLUIDS


Use mineral oil-based hydraulic fluids HL or HM type, according to ISO 6743-4. For these fluids, use NBR seals (code V). For fluids HFDR type (phosphate esters) use FPM seals (code V). For the use of other kinds of fluid such as HFA, HFB, HFC, please consult our technical department. Using fluids at temperatures higher than 80 °C causes a faster degradation of the fluid and of the seals characteristics.

The fluid must be preserved in its physical and chemical characteristics.


## 5 - PRESSURE DROPS $\Delta p$ -Q

(values obtained with viscosity 36 cSt at 50 °C)

### 5.1 - DSP10 pressure drops



### 5.2 - DSP11 pressure drops



## 6 - SWITCHING TIMES

The values indicated refer to a solenoid valve working with piloting pressure of 100 bar, with mineral oil at a temperature of 50°C, at viscosity of 36 cSt and with P→A / B→T connections.

The energizing and de-energizing times are obtained at the pressure variation which occurs on the lines.

### ACTUATED VALVE

SPOOL	FLOW DIRECTIONS				
	P→A	P→B	A→T	B→T	P→T
	CURVES ON GRAPH				
S1, SA1, SB1	1	1	1	2	
S2, SA2, SB2	2	2	3	4	
S3, SA3, SB3	1	1	3	4	
S4, SA4, SB4	1	1	2	4	
TA, TB	1	1	1	2	
TA02, TB02	2	2	3	4	
RK	1	1	1	2	

### NORMAL POSITION

SPOOL	FLOW DIRECTIONS				
	P→A	P→B	A→T	B→T	P→T
	CURVES ON GRAPH				
S2			3	4	3
S3			4	5	
S4					6

### ACTUATED VALVE

SPOOL	FLOW DIRECTIONS				
	P→A	P→B	A→T	B→T	P→T
	CURVES ON GRAPH				
S1, SA1, SB1	1	1	1	2	
S2, SA2, SB2	1	1	1	3	
S3, SA3, SB3	1	1	1	3	
S4, SA4, SB4	1	1	1	3	
TA, TB	1	1	1	2	
TA02, TB02	1	1	1	3	
RK	1	1	1	2	

### NORMAL POSITION

SPOOL	FLOW DIRECTIONS				
	P→A	P→B	A→T	B→T	P→T
	CURVES ON GRAPH				
S2			2	2	2
S3			4	4	
S4					5

TIMES (± 10%) [ms]	ENERGIZED		DE-ENERGIZED	
	2 Pos	3 Pos	2 Pos	3 Pos
AC solenoid	90	60	90	60
DC solenoid	130	100	90	60


## 7 - OPERATING LIMITS

The curves define the flow rate operating fields according to the valve pressure of the different versions. The values have been obtained according to ISO 6403 norm with solenoids at rated temperature and supplied with voltage equal to 90% of the nominal voltage, with pilot supply pressure of 10 bar

The value have been obtained with mineral oil, viscosity 36 cSt, temperature 50 °C and filtration according to ISO 4406.1999 class 18/16/13.

**Limits refer to the 4-port operation. The operating limits of a 4-port valve in 3-port operation, or with port A or B plugged, or without flow may reduce considerably.**

### 7.1 - DSP10




### DC SOLENOID VALVE

SPOOL	CURVE	
	P→A	P→B
S1, SA1, SB1	1	1
S2, SA2, SB2	2	2
S3, SA3, SB3	1	1
S4, SA4, SB4	2	2
TA, TB	1	1
TA02, TB02	1	1
RK	1	1

**NOTE:** Limits showed for S1, S3, TA / TB and RK spools are determined by the value of the piloting pressure (10 bar).

### 7.1 - DSP11



## 8 - ELECTRICAL FEATURES

### 8.1 - Solenoids

These are essentially made up of two parts: tube and coil. The tube is threaded into the valve body and includes the armature that moves immersed in oil, without wear. The inner part, in contact with the oil in the return line, ensures heat dissipation.

The coil is fastened to the tube by a threaded ring, and can be rotated 360°, to suit the available space.

**NOTE 1:** In order to further reduce the emissions, use of type H connectors is recommended. These prevent voltage peaks on opening of the coil supply electrical circuit (see cat. 49 000).

**NOTE 2:** The IP65 protection degree is guaranteed only with the connector correctly connected and installed.

<b>VOLTAGE SUPPLY FLUCTUATION</b>	± 10% Vnom
<b>MAX SWITCH ON FREQUENCY</b>	6.000 ins/hr
<b>DUTY CYCLE</b>	100%
<b>ELECTROMAGNETIC COMPATIBILITY (EMC) (NOTE 1)</b>	In compliance with 2014/30/EU
<b>LOW VOLTAGE</b>	In compliance with 2014/35/EU
<b>CLASS OF PROTECTION</b> Atmospheric agents (IEC 60529) Coil insulation (VDE 0580) Impregnation: DC valve AC valve	IP 65 ( <b>NOTE 2</b> ) class H class F class H

### 8.2 - Current and absorbed power for DC solenoid valve

The table shows current and power consumption values of the DC coils.

Using connectors type "D" (see cat. 49 000) with embedded bridge rectifier it is possible to feed DC coils (starting from 48V voltage) with alternating current (50 or 60 Hz), considering a reduction of the operating limits by 5 ÷ 10% approx.

(values ± 10%)

	Resistance at 20°C [Ω]	Current consumption [A]	Power consumption [W]	Coil code
				K1
<b>D12</b>	4.4	2.72	32.7	1903080
<b>D24</b>	18.6	1.29	31	1903081
<b>D48</b>	78.6	0.61	29.5	1903083
<b>D110</b>	436	0.26	28.2	1903464
<b>D220</b>	1758	0.13	28.2	1903465

### 8.3 - Current and absorbed power for AC solenoid valve

The table shows current and power consumption values at inrush and at holding, relevant to the different coil types for AC current.

(values ± 5%)

Suffix	Nominal Voltage [V]	Freq. [Hz]	Resistance at 20°C [Ω]	Current consumption at inrush [A]	Current consumption at holding [A]	Power consumption at inrush [VA]	Power consumption at holding [VA]	Coil Code K1
<b>A24</b>	24	50	1,69	5,81	1,32	139	32	1902830
<b>A48</b>	48		6,02	3,78	0,86	182	41	1902831
<b>A110</b>	110V-50Hz 120V-60Hz	50/60	33	1,76	0,40	194	44	1902832
				1,54	0,35	185	42	
<b>A230</b>	230V-50Hz 240V-60Hz		135	0,92	0,21	213	48	1902833
				0,79	0,18	190	43	
<b>F110</b>	110	60	28,5	1,45	0,33	160	36	1902834
<b>F220</b>	220		103	0,92	0,21	203	46	1902835

## 9 - ELECTRIC CONNECTORS

Solenoid valves are delivered without connectors. Connectors can be ordered separately. See catalogue 49 000.

## 10 - MAX PRESSURES

Max pressure in P, A, B ports	bar	350
Minimum pilot supply pressure <b>NOTE</b>		10
Max pressure in T line with external drain		300
Max pressure in Y line with external drain		210 (DC) / 160 (AC)
Max pressure in T line with internal drain		210 (DC) / 160 (AC)

**NOTE:** The valve needs a difference of at least +10 bar between the pilot pressure and the discharge/drainage pressure In order to work correctly.


## 11 - PILOT AND DRAIN

The valves with electro-hydraulic actuation (DSP) are available with both pilot supply and drain internal or external. The version with external drain allows a higher back pressure on the return line.

The pilot supply Z type consists of an arrangement with internal piloting and 30 bar supply pressure for the pilot stage by means of a fixed adjustment pressure reducing valve .

The valves with hydraulic actuation (DSC) are available with external pilot supply and external drain only.

**NOTE:** The pilot supply and drainage configuration must be chosen when ordering. Subsequent modification is only permitted by authorized experienced operators or at the factory.




**X:** plug M6x8 for external pilot  
**Y:** plug M6x8 for external drain


TYPE OF VALVE		Plug assembly	
		X	Y
<b>IE</b>	internal pilot and external drain	NO	YES
<b>II</b>	internal pilot and internal drain	NO	NO
<b>EE</b>	external pilot and external drain	YES	YES
<b>EI</b>	external pilot and internal drain	YES	NO



## 12 - OVERALL AND MOUNTING DIMENSIONS FOR DSP10 AND DSP11




### 13 - OVERALL AND MOUNTING DIMENSIONS FOR DSC10 AND DSC11



### 14 - MOUNTING INTERFACES


#### DS\*10

ISO 4401-10-09-0-05  
(CETOP 4.2-4-10-350)



#### DS\*11

ISO 4401-10-09-0-05  
(CETOP 4.2-4-10-350)  
deviating from standard:  
P, T, A, B ports Ø48




## 15 - INSTALLATION

Configurations with centering and recall springs can be mounted in any position; type RK valves - without springs and with mechanical detent - must be mounted with the longitudinal axis horizontal.

Valve fastening takes place by means of screws or tie rods, laying the valve on a lapped surface, with values of planarity and smoothness that are equal to or better than those indicated in the drawing.

If the minimum values of planarity or smoothness are not met, fluid leakages between valve and mounting surface can easily occur.




## 16 - OPTIONS

### 16.1 - Control of the main spool stroke: C

Stroke control for the main spool is possible by means of special side covers so as to vary the maximum clearance opening.

This solution allows control of the flow rate from the pump to the actuator and from the actuator to the outlet, obtaining a double adjustable control on the actuator.


Add the letter **C** in the identification code to order this version (see point 1).



### 16.2 - Control of the main spool shifting speed: D

By placing a double flow control valve (MERS type) between the pilot solenoid valve and the main stage, the pilot supply flow can be adjusted and therefore the changeover smoothness can be varied.


Add the letter **D** in the identification code to order this version (see point 1).



### 16.3 - Subplate with throttle on line P

It is possible to introduce a subplate with a restrictor of  $\varnothing 1.5$  on line P between the pilot solenoid valve and the main stage.


Add **P15** in the identification code to order this version (see point 1).



## 17 - MANUAL OVERRIDE

Whenever the solenoid valve installation may involve exposure to atmospheric agents or use in tropical climates, a boot protected manual override is recommended.

Add **/CM** at the end of the identification code to order this version (see point 1).





# DSP1\*

**DUPLOMATIC**  
MOTION SOLUTIONS  
*a member of **DAIKIN** group*

**DUPLOMATIC MS Spa**

via Mario Re Depaolini, 24 | 20015 Parabiago (MI) | Italy

T +39 0331 895111 | E vendite.ita@duplomatic.com | sales.exp@duplomatic.com  
duplomaticmotionsolutions.com